

**CERTIFICATE OF COMPLIANCE**



**EL Class I**

*Date of issue: 23 July 2019*

*Valid until: 23 July 2024*

*EHEDG hereby declares that the product*


***Pump HYCARE HY4 type with EPDM gasket, NBR stator and Sic/Sic mechanical seal (range EH 6HY12/ 6HY24 / 13HY6 / 13HY12 / 3HY24)***

*from*

*PCM EUROPE SAS, 1 rue René Moineau , 49123 CHAMPTOCE SUR LOIRE, France*

*has/have been evaluated for compliance and meets/meet the current criteria for Hygienic Equipment Design of the EHEDG*

***Certificate No. EHEDG-C1900011***

Signed  \_\_\_\_\_ *President EHEDG*  
*Hein Timmerman*

Signed  \_\_\_\_\_ *EHEDG Certification Officer*  
*Karlijn Faber*

*EHEDG  
Karspeldreef 8  
1101 CJ Amsterdam  
Netherlands*

©EHEDG

# Appendix 3

## EHEDG Certification – Equipment Evaluation Form

Date: 23.07.2019

EHEDG File Number: EHEDG-C1900011

Certification Type: EL CLASS I

Applicant : PCM EUROPE SAS, France

Equipment: Positive displacement pump

Type or model No/s.: HYCARE type HY4, with EPDM gasket, NBR stator and Sic/Sic mechanical seal.

Other essential identification: range 6HY12 EH/ 6HY24 EH/ 13HY6 EH/ 13HY12 EH/ 3HY24 EH

### Evaluated by:

Name: Nicolas ROSSI [AEO]

### Approved by:

Name: Jürgen Hofmann

Title: [AEO]

Date, Signature: 23.07.2019



1. Results of inspection for compliance with the EHEDG Hygienic Design Criteria.

Conclusion:

YES

**The equipment complies with the criteria.**

**The use of the EHEDG Certification logo is justified:**

MAYBE

2. Evidence for compliance provided and convincing for Certification.

Conclusion:

YES

**The equipment complies with the criteria where possible.**

**The use of the EHEDG Certification logo is justified:**

Signature:



Date: 23/07/2019

*The original of this form will be kept by EHEDG together with the application, the inspection report, the evidence provided and any other relevant documentation, as listed on the back.*

## Appendix 3

### EHEDG Certification – Equipment Evaluation Form

No.	Description
1	EHEDG Certificate of Compliance
2	Contract to use the EHEDG Certification Logo for equipment
3	Appendix 1: Equipment intended for cleaning in place with liquids without dismantling
4	Appendix 2: Conditions for use of the EHEDG Certification Logo
5	Appendix 3: Equipment evaluation form
6	Evaluation report of the design :positive displacement pump Hycare type 4 (range 6HY12 EH/ 6HY24 EH/ 13HY6 EH/ 13HY12 EH/ 3HY24 EH ) with EPDM gasket, NBR stator and Sic/Sic mechanical seal  no 006ACT2019
7	Drawings and technical detail of the HYCARE 13HY12 (M 002762 A)  Original stamped
8	Test report no. 263/10.09.2010. (TUM)
9	Example Logo EL class I