

**CERTIFICATE OF COMPLIANCE**



**EL Class I**

*Date of issue: 11 November 2019*

*Valid until: 10 November 2024*

*EHEDG hereby declares that the product*


***optical In-line Spectrometer Memosens Wave CKI50 with PEEK profiled gaskets and FFKM sealing***

*from*

*Endress+Hauser Conducta GmbH+Co. KG, Dieselstrasse 24 , 70839 Gerlingen, Germany*

*has/have been evaluated for compliance and meets/meet the current criteria for Hygienic Equipment Design of the EHEDG*

***Certificate No. EHEDG-C1900174***

Signed  \_\_\_\_\_ *President EHEDG*  
*Hein Timmerman*

Signed  \_\_\_\_\_ *EHEDG Certification Officer*  
*Karlijn Faber*

*EHEDG  
Karspeldreef 8  
1101 CJ Amsterdam  
Netherlands*

©EHEDG

## Appendix 3

# EHEDG Certification – Equipment Evaluation Form

Date: 31.07.2019

EHEDG File Number: EHEDG-C1900174

Certification Type: EL CLASS I

Applicant: Endress+Hauser Conducta GmbH+Co. KG

Equipment: Optical In-line Spectrometer

Type or model No/s.: Memosens Wave CKI50 with PEEK profiled gaskets and FFKM sealing

Other essential identification: 2 mm, 5 mm, 10 mm path length

### Evaluated by:

Name: Dr. Jürgen Hofmann

### Approved by:

Name: Shih Rong Huang

Title: [AEO]

Date, Signature: Willy Shih-Rong Huang 10.12.2019

1. Results of inspection for compliance with the EHEDG Hygienic Design Criteria.

Conclusion:

**The equipment complies with the criteria.**

YES

**The use of the EHEDG Certification logo is justified:**

MAYBE

2. Evidence for compliance provided and convincing for Certification.

Conclusion:

**The equipment complies with the criteria where possible.**

YES

**The use of the EHEDG Certification logo is justified:**

Signature: J. Hofmann

Date: 11.11.2019

*The original of this form will be kept by EHEDG together with the application, the inspection report, the evidence provided and any other relevant documentation, as listed on the back.*

### Appendix 3

No.	Description
1.	EHEDG Certificate of Compliance
2.	Contract to use the EHEDG Certification Logo for equipment
3.	Appendix 1: Equipment intended for cleaning-in-place with liquids without dismantling
4.	Appendix 2: conditions for use of the EHEDG Certification Logo
5.	Appendix 3: Equipment evaluation form
6.	Evaluation report of the design of the optical In-line Spectrometer Memosens Wave CKI50 with PEEK profiled gaskets and FFKM sealing, no. 676TUM2019
7.	Drawings of the optical In-line Spectrometer Memosens Wave CKI50 with PEEK profiled gaskets and FFKM sealing, drawing no. 433460 original stamped
8.	Test report of the in-place cleanability test method, no. 676/20.05.2019
9.	Example of EHEDG Certified Logo Type EL CLASS I