

# CERTIFICATE OF COMPLIANCE



**EL Class II**

*Date of issue: 18 September 2024*

*Valid until: 31 December 2025*

*EHEDG hereby declares that the product*

***rotary feeder ZS ECT II, type 6323 in sizes 150/225, 250/300, 200/350, 250/360, 250/450, 300/470 with silicone and HPU gaskets and PTFE shaft sealing***

*from*

*JAUDT Dosiertechnik Maschinenfabrik GmbH, Raiffeisenstrasse 3-5 , 86167 Augsburg, Germany*

*has/have been evaluated for compliance and meets/meet the current criteria for Hygienic Equipment Design of closed process applications of the EHEDG*

***Certificate No. EHEDG-C2400038***

Signed \_\_\_\_\_ *Hein Timmerman* \_\_\_\_\_ *President EHEDG*

Signed \_\_\_\_\_ *Karlijn Faber* \_\_\_\_\_ *EHEDG Certification Officer*

***EHEDG  
Karspeldreef 8  
1101 CJ Amsterdam  
Netherlands***

***©EHEDG***



## APPENDIX 3 EHEDG Certification – Equipment Evaluation Form

Design Evaluation Date: 02.02.2024

EHEDG File Number: EHEDG-R2400007

Certification Type: EL CLASS II

Applicant: JAUDT Dosiertechnik Maschinenfabrik GmbH

Equipment: rotary feeder ZS ECT II, type 6323 in sizes 150/225, 250/300, 200/350, 250/360, 250/450, 300/470 with silicone and HPU gaskets and PTFE shaft sealing

Other essential identification:

**Evaluated by:**

Name: Dr. Jürgen Hofmann

Date, Signature: 22.08.2024

**Approved by:**

Name: Andy Timperley, Chairman on behalf of the SubCom Certification

Date, Signature: 16.09.2024,

The use of the EHEDG Certification logo is justified based on the results of the design evaluation, inspection, and testing (as applicable) of the equipment for compliance with the current EHEDG Hygienic Design Criteria (HDC):

Criteria	Certification for <b>use in Closed Processes</b>
<input checked="" type="checkbox"/>	The equipment complies with all applicable HDC in the Guidelines.
<input type="checkbox"/>	Evidence for compliance required and provided by in-place cleanability test method according to EHEDG Doc. 2.
<input type="checkbox"/>	Evidence for compliance required and provided by in-place cleanability test method according to EHEDG Doc. 2, in-place sterilisability test method according to EHEDG Doc. 5, and bacteria tightness test according to EHEDG Doc. 7 for <b>EL ASEPTIC</b> Certification.
Criteria	Certification for <b>use in Open Processes</b>
<input type="checkbox"/>	The equipment complies with all applicable HDC in the Guidelines.
<input type="checkbox"/>	Evidence for compliance required and provided by OPC cleanability test method according to EHEDG Doc. 57.

## APPENDIX 3

No.	Description
1.	EHEDG Certificate of Compliance
2.	Contract to use the EHEDG Certification Logo for equipment
3.	Appendix 1: Equipment intended for cleaning-out-of-place with liquids
4.	Appendix 2: conditions for use of the EHEDG Certification Logo
5.	Appendix 3: Equipment evaluation form
6.	Evaluation report of the design of the rotary feeder ZS ECT II, type 6323 in sizes 150/225, 250/300, 200/350, 250/360, 250/450, 300/470 with silicone and HPU gaskets and PTFE shaft sealing, no. 30424TUM2024
7.	Drawings of the rotary feeder ZS ECT II, type 6323 in sizes 150/225, 250/300, 200/350, 250/360, 250/450, 300/470 with silicone and HPU gaskets and PTFE shaft sealing, drawing nos. 6323-EHEDG Rev. A page 1 – 4; 104630.0862, 107630.0617; original stamped
8.	Cleaning and Installation manual no. BA6323.0002_EN_Rev3 supplied by the manufacturer
9.	Example of EHEDG Certified Logo Type EL CLASS II